


# PP-Mg:SLT Lineup

Available for UV, Visible - MIR Range with High Conversion Efficiency


## Available Range of PP-Mg:SLT \*




\*PP-Mg:SLT  
(Periodically poled Mg-doped stoichiometric LiTaO<sub>3</sub>)

## Standard PP-Mg:SLT for 1064nm SHG


SHG output power	>1W
Maximum input capacity	>10W
Non-linear Coefficient (deff)	> 7.5pm/V
Phase matching temperature	40+/- 10 degree C
AR Coat	S1&S2 R<0.5% @ 1064/532nm
Crystal Size (T x W)	0.5mm x 2mm
Crystal Length (L)	10mm, 30mm



## Customized PP-Mg:SLT



## Accessories



\*Mount size is adjusted to the device size.

Sample mount with TEC

5-axis stage

Temperature controller

Dichroich Mirror  
(R:1064nm,532nm / T:355nm)  
(R:1064nm / T:532nm)

**OXIDE**

**OXIDE Corporation**

1747-1 Maginohara, Mukawa, Hokuto, Yamanashi 408-0302 JAPAN  
Tel: +81-551-26-0022, Fax: +81-551-26-0033



Sales@opt-oxide.com

<https://www.opt-oxide.com>

Oxide Yamanashi